

**BSN O1839**



: BSN Thermprozesstechnik

**Product number:**  
 O1839

## Description

<span style="border: 1px solid black; display: inline-block; width: 20px; height: 15px;"></span>	
<span style="border: 1px solid black; display: inline-block; width: 20px; height: 15px;"></span>	BSN Therm
<span style="border: 1px solid black; display: inline-block; width: 20px; height: 15px;"></span>	<span style="border: 1px solid black; display: inline-block; width: 20px; height: 15px;"></span>
<span style="border: 1px solid black; display: inline-block; width: 20px; height: 15px;"></span>	2016
<span style="border: 1px solid black; display: inline-block; width: 20px; height: 15px;"></span>	
<span style="border: 1px solid black; display: inline-block; width: 20px; height: 15px;"></span>	465 °C
<span style="border: 1px solid black; display: inline-block; width: 20px; height: 15px;"></span>	<span style="border: 1px solid black; display: inline-block; width: 20px; height: 15px;"></span>
<span style="border: 1px solid black; display: inline-block; width: 20px; height: 15px;"></span>	401 <span style="border: 1px solid black; display: inline-block; width: 10px; height: 15px;"></span>
<span style="border: 1px solid black; display: inline-block; width: 20px; height: 15px;"></span>	239 <span style="border: 1px solid black; display: inline-block; width: 10px; height: 15px;"></span>
<span style="border: 1px solid black; display: inline-block; width: 20px; height: 15px;"></span>	124 <span style="border: 1px solid black; display: inline-block; width: 10px; height: 15px;"></span>
<span style="border: 1px solid black; display: inline-block; width: 20px; height: 15px;"></span>	2.41 <span style="border: 1px solid black; display: inline-block; width: 10px; height: 15px;"></span> / <span style="border: 1px solid black; display: inline-block; width: 10px; height: 15px;"></span>
<b>LGO</b> <span style="border: 1px solid black; display: inline-block; width: 20px; height: 15px;"></span>	
<span style="border: 1px solid black; display: inline-block; width: 20px; height: 15px;"></span>	6000 <span style="border: 1px solid black; display: inline-block; width: 10px; height: 15px;"></span>
<span style="border: 1px solid black; display: inline-block; width: 20px; height: 15px;"></span>	3351 <span style="border: 1px solid black; display: inline-block; width: 10px; height: 15px;"></span>

□□□□	3800 □□
<b>LGO □□□□</b>	
□□	4410 □□
□□	1040 □□
□□□□	780 □□
□□□□	2 □
□□□□	□□□
□□□□	□□□□□
□□□□□	□□□
□□□□□□□	
□□	4050 □□
□□	4253 □□
□□□□	6743 □□
□□□□□□□	
□□	1800 □□
□□	1000 □□
□□□□	675 □□
□□□□□□□	
□□□□	1 □
<b>LGO □□□□</b>	
□□	□□
□□□□□	3 □
1 □	2 □□□□ 50 □□
2 □	□□ 1 □ 50 □□
<b>LGO □□</b>	
□□ □□	540 °C
□□□□	465 °C

□□□□□□□□

± 3 K

LGO □□□

□□□□□□

6 □

□□□□□□

1/2 □

□□□

□□

□□

□□□□

